



FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



PART NUMBER: M36-A-11D-UL

MATERIALS:
1.BODY: PA
2.TERMINAL TYPE: UL1007 22AWG.

RANGE OF APPLICATION: FOR ONPOW61 SERIES

SPECIFICATIONS:
1.GENERAL TOLERANCE:0-18mm=±0.43, 18-80mm=±0.62.

BRAND 品牌		红波按钮制造有限公司		
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.		
TITLE 名称	QUICK CONNECT SOCKET			UNIT 单位 mm
DWG NO. 图号	M36-A-11D-UL		SCALE 比例 1.5 : 1	SIZE 图纸 A4
FILE NAME 档案名称	M36-A.DWG	DRAWN 制图	YDY 2024/12/11	SHEET 张 1/1
		REV. 版本		V1.0