







P/N LEGEND

A2542	HA	XP	N	0	W	NP	N	00	G
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩
① Series No.									
② Connector type: HA=Housing A Type									
③ No. of circuits									
④ N=Halogen Free									
⑤ Material: 0=Nylon 66-V0									
⑥ Color: W=White									
⑦ Plating code: NP=Non-plating									
⑧ Plating code: N=Non-plating									
⑨ Option code: 00=Standard									
⑩ Packing code: G=Bag									

SPECIFICATIONS

Current Rating: 4A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: 1000V AC/minute

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
02P	2.54	5.68	12P	27.94	31.08
03P	5.08	8.22	13P	30.48	33.62
04P	7.62	10.76	14P	33.02	36.16
05P	10.16	13.30	15P	35.56	38.70
06P	12.70	15.84	16P	38.10	41.24
07P	15.24	18.38	17P	40.64	43.78
08P	17.78	20.92	18P	43.18	46.32
09P	20.32	23.46	19P	45.72	48.86
10P	22.86	26.00	20P	48.26	51.40
11P	25.40	28.54			



燦達電子工業股份有限公司
JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT SCALE SHEET
mm 1 : 1 1 of 1

DRAWN BY 劉建芳
2017.09.29

APPROVED BY 謝瑞清
2017.09.29

GENERAL TOLERANCE

A1 X.X±0.25
A0 NEW RELEASE 2017.09.29 劉建芳
REV. DESCRIPTION DATE NAME X.XXX±0.05

TITLE:
2.50mm PITCH
HOUSING
DRAW NO.: A2542HA-XPXXXXXXX REV. A1