






P.C.B. LAYOUT








P/N LEGEND

C5080 WR-04P XXX			
①	②	③	④
① Series No.			
② Connector type: WR=Right angle			
③ No. of circuits			
④ Option code:			
Blank=Nylon6T,V=0; Color: Natural(Black)			

SPECIFICATIONS

Current Rating: 10A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: 1500V AC/minute
Pin Material: Brass/Tin-plated
Metal Band: Brass/Tin-plated



							燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
				UNIT	SCALE	SHEET	TITLE: P/N:C5080WR-04P 5.08mm PITCH 90° WAFER			
				mm		1 of 1				
				DRAWN BY		APPROVED BY				
				歐陽小強		董正一				
				2007.04.25		2007.04.25				
				GENERAL TOLERANCE						
A2	EN202410221797	2024.10.22	廖琴琴	GENERAL TOLERANCE			DRAW NO. : C5080WR-04P			REV. A2
A1	EN1107280313	2011.07.28	肖勇	X. X±0. 25						
A0	NEW RELEASE	2007.04.25	董正一	X. XX±0. 15						
REV.	DESCRIPTION	DATE	NAME	X. XXX±0. 05						
										