





P/N LEGEND

A1250	WV	XP	N	X	X	XX	N	00	B
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩
① Series No. ② Connector type: WV=Vertical ③ No. of circuits ④ N=Halogen Free ⑤ Material: L=LCP-V0 ; 6=Nylon 6T ⑥ Color: B=Black N=Natural ⑦ Plating code for contacts: T1=Tin-plated S4=Gold-plated 10u"on contact area, Gold-flash on solder area ⑧ Plating code: N=Non-plating ⑨ Option code: 00=Standard ⑩ Packing code: B=Tray									

SPECIFICATIONS

Current Rating: 1A AC,DC
Voltage Rating: 125V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 20MΩ Max.
Insulation Resistance: 100MΩ Min.
Withstanding Voltage: 500V AC/minute
Pin Material: Phosphor Bronze

Circuit NO.	Dimensions		Circuit NO.	Dimensions	
	A	B		A	B
02P	1.25	4.25	11P	12.50	15.50
03P	2.50	5.50	12P	13.75	16.75
04P	3.75	6.75	13P	15.00	18.00
05P	5.00	8.00	14P	16.25	19.25
06P	6.25	9.25	15P	17.50	20.50
07P	7.50	10.50	16P	18.75	21.75
08P	8.75	11.75	17P	20.00	23.00
09P	10.00	13.00	18P	21.25	24.25
10P	11.25	14.25			

								燦達電子工業股份有限公司			
								JOINT TECH ELECTRONIC IND. CO., LTD.			
				UNIT	SCALE	SHEET	TITLE:				
				mm	1 : 1	1 of 1					
				DRAWN BY		APPROVED BY					
A4	EN202503131903	2025. 03. 13	樊翠鳳	周傑亮		張子波		1. 25mm PITCH 180° WAFER			
A3	EN20200601294	2020. 05. 22	周傑亮	2013. 11. 15		2013. 11. 15					
A2	EN1411100001	2014. 11. 10	劉建芳	GENERAL TOLERANCE							
A1	EN1408220004	2014. 08. 22	黃培軍	X. X±0. 25		ANGLE±					
A0	NEW RELEASE	2013. 11. 15	周傑亮	X. XX±0. 15							
REV.	DESCRIPTION	DATE	NAME	X. XXX±0. 05							
				DRAW NO. :				A1250WV-XPNXXXXXXXXXB			
								REV. A4			