








02P~04P pin kink location
(The two on the side)



05P~15P pin kink location
(In the second from the edge in)



MATED CONDITION



P.C.B. LAYOUT
(TOP VIEW)

P/N LEGEND

A1500	WV	XP	N	O	X	XX	N	KO	G
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩
① Series No.									
② Connector type: WV=Vertical									
③ No. of circuits									
④ N=Halogen Free									
⑤ Material: 0=Nylon 66+15%GF,UL94V-0									
⑥ Color: W=White ; B=Black									
⑦ Plating code for contacts: T1=Tin-plated M1=Matte Tin-plated									
⑧ Plating code: N=Non-plating									
⑨ Option code: KO=With pin kink									
⑩ Packing code: G=Bag									

SPECIFICATIONS

Current Rating: 1A AC,DC
Voltage Rating: 100V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 20MΩ Max.
Insulation Resistance: 500MΩ Min.
Withstanding Voltage: 500V AC/minute
Pin Material: Brass

Circuit No.	Dimensions		
	A	B	C
02P	1.50	4.50	3.75
03P	3.00	6.00	5.25
04P	4.50	7.50	6.75
05P	6.00	9.00	8.25
06P	7.50	10.50	9.75
07P	9.00	12.00	11.25
08P	10.50	13.50	12.75
09P	12.00	15.00	14.25
10P	13.50	16.50	15.75
11P	15.00	18.00	17.25
12P	16.50	19.50	18.75
13P	18.00	21.00	20.25
15P	21.00	24.00	23.25



燦達電子工業股份有限公司
JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT	SCALE	SHEET
mm	1 : 1	1 of 1
DRAWN BY 童冠銘	APPROVED BY 吳國維	
2011.06.01	2011.06.01	
GENERAL TOLERANCE		
X. X±0.25 X. XX±0.15 X. XXX±0.05	ANGLE± 	

TITLE:

1.50mm PITCH
180° WAFER

DRAW NO. :	REV. A4
A1500WV-XPNNXXXXXKX	