






P/N LEGEND

C5080	WV-04P	N	X	X	T1	N	00	B
①	②	③	④	⑤	⑥	⑦	⑧	⑨
① Series No.								
② Connector type: WV=Vertical								
③ No. of circuits								
④ N=Halogen Free								
⑤ Material: 2=Nylon66-V2; 0=Nylon66-V0								
L=LCP-V0								
⑥ Color: B=BlackN=Natural W=White								
⑦ Plating code for contacts: T1=Tin-plated								
⑧ Plating code: N=Non-plating								
⑨ Option code: 00=Standard								
⑩ Packing code: B=Tray								

SPECIFICATIONS

Current Rating: 10A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: 1500V AC/minute
Pin Material: Brass/Tin-plated



				JOINT TECH ELECTRONIC IND. CO., LTD.			5.08mm PITCH 180° WAFER
				UNIT	SCALE	SHEET	
				mm	1 : 1	1 of 1	
				DRAWN BY 李華明 2019.12.13	APPROVED BY 謝瑞清 2019.12.13		
A3	EN202410221797	2024.10.22	廖琴琴	GENERAL TOLERANCE			
A2	EN20210421611	2021.04.21	黃潮				
A1	EN1703140004	2016.03.14	賴永強	X. X±0. 25	ANGLE±		
A0	NEW RELEASE	2014.08.13	黃模有	X. XX±0. 15 X. XXX±0. 05			
REV.	DESCRIPTION	DATE	NAME	DRAW NO. : C5080WV-04PNXXXXXXXXX		REV. A3	