

DIGITUS USB M.2 hard disk enclosure, SSD, external, NVMe , 20Gbps, USB 3.2 Gen2x2, aluminum, incl. mounting material

DA-71157

EAN 4016032497486



USB hard drive enclosure, external, NVMe 20Gbps, USB 3.2 Gen 2x2, aluminum, tooling

The DA-71157 USB hard disk enclosure is a high-speed marvel for NVMe SSDs, designed for maximum performance and efficiency. With impressive data transfer rates of 20 Gbps for NVMe, it offers an optimal solution for lightning-fast file transfers and seamless performance. The USB 3.2 Gen2x2 interface allows for maximum flexibility and backwards compatibility with previous USB versions. With support for M.2 modules in the 2230, 2242, 2260 and 2280 formats and a maximum storage capacity of 8 TB, it is the ideal choice for economical and high-performance storage solutions. The tool-free design allows for easy installation, while the robust ASM2364 chipset ensures reliable performance. With its durable aluminum housing and integrated LED indicator, the enclosure provides excellent passive heat dissipation and convenient status monitoring. Compact, lightweight and with plug-and-play support, it is perfect for mobile use. Compatible with a wide range of operating systems and USB-C products, it offers maximum versatility and adaptability for every need.

The DA-71157 M.2 NVMe SSD enclosure will become your preferred solution for high capacity storage up to 20 Gbps. This elegant, tool-less enclosure supports mini SSDs in M.2 B+M key format.

- Supported Mini SSD in format: M.2, M Key, B+M Key(NVMe)
- Supported storage technology: NVMe
- Max. supported capacity: 8TB
- Installation method: simple, quick installation with included mounting material

- Data transfer rate: NVMe: 20 Gbit/s
- Supports M.2 modules in the format: 2230, 2242, 2260, 2280
- Supported keys: M Key, B+M Key (NVMe)
- USB 3.2 Gen2x2
- Backwards compatible with USB: 3.1 / 3.0 / 2.0 / 1.1
- Chipset: ASM2364
- LED activity indicator: yes
- Housing: Aluminum
- Heat dissipation: passive
- Supports Plug & Play
- Power supply via USB connection
- Supports Win 11, 10, 8, 7
- Supports: Android / iOS
- Supports macOS , Linux 2.4.x or higher, Google Chrome OS 9.x or higher
- Operating temperature: 5 to 50°C
- Storage temperature: -40 to 70°C
- Humidity during operation: 5 to 90% (non-condensed)
- 100x42x15mm
- Weight: 100g
- Color: Pantone 430C
- USB-C products: yes

Package contents

- External SSD enclosure, M.2 - USB Type-C™
- USB cable (C - C), 25 cm
- Mini screwdriver + screws
- QIG

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	50	8.75	40.00	48.00	17.00	32,640.00
Packaging Unit Inside	1	0.18	0.00	0.00	0.00	0.00
Packaging Unit Single	1	0.18	15.30	9.50	3.70	537.80
Net single without Packaging	1	0.13	15.30	9.50	3.70	537.80

More images:



Safety notes

- Overloading can lead to overheating and damage to the appliance or the connected peripherals.
- If necessary, use an external power supply to ensure stable performance.
- If devices such as external hard disks or printers that require a high power consumption are connected, the device should be used with an external power supply. Otherwise, the device could be overloaded or functional problems could occur.
- Do not expose the device to rain, moisture, vapors or liquids.
- Do not insert any objects into the device.
- Do not attempt to repair the unit or open the housing without authorization. You risk an electric shock!
- Ensure adequate ventilation to prevent damage due to overheating.
- Dust, moisture, vapors and strong cleaning agents or solvents can cause damage to the device.
- Disconnect the appliance from the power supply and the connected devices before cleaning.
- Clean the device with a dust-free cloth.

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com