




IP68 快速防水接线器/Quick waterproof connector

M684-E 公母对插/Male and Female



备注: 以上  标注3点在一条线即可快速插拔






产品参数/Technical data

型号 Model	M684-E	
材料 Material	防火阻燃 Fire and flame retardant UL94V-2	
额定输出 Rated output	IEC/NSW:24A 450VAC ETL:10A 300VAC	
防护等级 IP code	IP68	
接线内芯 Terminal	2P/3P	
工作温度 Working	T105	
接线范围 Rated connecting capacity	欧规 European:0.5 ~ 2.5mm² 澳规 Australia:0.5 ~ 2.5mm² 美规 American:SJOW 14-18AWG	
密封胶塞/seal plug		
胶塞孔径/plug aperture	8mm	11mm
适用线径/Available cable diameter (橡胶圆线/Round rubber cable)	2*M20(4-8mm)	2*M20(6-11mm)
防水测试 Testing	20M 150hours	
参考剥线长度 Refer to stripping length	10mm (0.5~1.0mm²) rigid 15mm (1.5~2.5mm²) rigid	
产品尺寸 Product Size(参考实际尺寸图)	110.36*25.02mm (Refer to actual drawing)	
认证 Certification	ENEC,CE,UKCA,ETL,NSW,CB,ROHS	
产品质保/Product warranty	1 年/ one year	
产品应用/Application	水底/Underwater(淡水 fresh water) 地埋/Underground	
注/Mark: 1.不能使用在盐碱土壤/Do not use in saline soil 2.不能长期接触油性物质或浸泡在油污中/Do not contact oily substances or soak in oil for a long time 3.不建议长期在日照暴晒下使用/Long time exposed under sunshine is not recommended		



产品图纸/Product drawings



0.5-1.0mm²



1.5-2.5mm²



参考剥线长度
Refer to stripping length

接线步骤/Wiring steps

01

扭开两端螺帽套筒,取出接线内芯

Open the nut cover at both end sides,take out quick connector



02

将电缆穿过螺帽主体,扳起卡扣

Thread the cable through the nut body and pull up the buckle



03

两端电缆线相对应插入自锁接线内芯
将卡扣压合锁住线材即可

Connect the wires to the 3 core pressed terminal correspondantly
press the levers



04

拧紧两端螺帽主体,接线完成

Twist and tighten the cable glands

