



Qoltec Pigtail fiber optic SC / UPC | Singlemode | 9/125 | G657A | 1m

Product code: 54428

Single-mode optical pigtail

Connectors: SC / UPC

Standard: G657A

Cable diameter: 0.9 mm

Cable length: 2 m

CONFIDENCE CONFIRMED BY A WARRANTY

Do you want a high quality product? Our solutions will meet your expectations. Fiber optic pigtails offered by us are covered by a 24-month guarantee valid from the date of purchase.

Technical data

Producer	Qoltec
Type connectors	SC/UPC
Type pigtail	Singlemode
Standard fiber	G657A2
Fiber core diameter	9/125 m
Sheath	LSZH
Diameter cable	0.9 mm
Insertion loss	<0.3 dB
Return loss	>55 dB
Cable length	1 m
Colour	Blue, white
Additional information	Easy installation and operation of optical fiber, high data transmission speed. LSZH - non-flammable outer cable sheath that does not emit harmful gases during a fire. The product is individually tested.
Package	Polybag
Net weight	0,0030 kg
Gross weight	0,0080 kg
Warranty	24 months
EAN code	5901878544281