



Qoltec Pigtail fiber optic LC/UPC | Singlemode | 9/125 | G657A2 | 2m

Product code: 54438

Pigtail fiber optic singlemode

Connectors: LC/UPC

Standard: G657A2

Diameter cable: 0.9 mm

Cable length: 2 m

CONFIDENCE CONFIRMED BY A WARRANTY

Do you want a high quality product? Our solutions will meet your expectations. Fiber optic pigtails offered by us are covered by a 24-month guarantee valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Type pigtail	Singlemode
Type connectors	LC/UPC
Standard fiber	LSZH
Fiber core diameter	9/125 m
Sheath	LSZH
Diameter cable	0.9 mm
Insertion loss	<0.3 dB
Return loss	>60 dB
Cable length	2 m
Colour	White
Additional information	Easy installation and handling on high speed fiber optical transmission networks. LSZH - Outside fireproof cable sheath, which the fire does not emit harmful gases. The product individually tested.
Package depth / length [mm]	180
Package width [mm]	200
Package height [mm]	10
Package	Polybag
Net weight [kg]	0.0050
Gross weight [kg]	0.0070
Warranty	24 months
EAN code	5901878544380