



HPX DUCT TAPE 1900



HPX DUCT TAPE 1900 is a duct tape for general purpose applications. Thanks to the strong initial tack and good adhesive strength, it adheres perfectly to PE and PP, among others.

Applications

- Repair, seal, bond, protect and bundle.
- Suitable for both smooth and rough surfaces such as stainless steel, glass, wood and polyethylene.
- Indoor and outdoor use.

Construction

Adhesive	synthetic rubber
Carrier	polyester/cotton cloth

Technical details

Thickness	0,17 mm
Adhesive strength	20 N/25 mm
Tensile strength	75 N/25 mm
Service temperature range	-10°C to +60°C
Short term temperature	+75°C

Art. No.	width	length	colour	Pack.	EAN code
DC5050	48 mm	50 m	silver	24	5425014223316
DC7550	75 mm	50 m	silver	16	5425014224689

Recommendations for use

Temperature: between 10°C and 35°C. The surface should be clean, dry, free of dust and grease. Avoid touching the adhesive side of the tape during the application to avoid affecting its performance. Apply pressure-sensitive tapes under maximum pressure to achieve the optimum pressure level. The indicated performance level is reached after an adhesion time of 24 hours at +23°C.

Storage and shelf life

Clean and dry in a well-ventilated area, preferably at a temperature between +10°C and +30°C. Stored under these conditions, the shelf life will be at least 12 months.

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu
Latest version 03/05/2021