



HPX GAFFER TAPE MATT BLACK 6400



HPX GAFFER TAPE MATT BLACK 6400 is a high-quality linen tape with a non-reflective, matt black surface. This tape is suitable for audio-visual applications.

Applications

- Suitable for theatres and film studios: non-reflective and light-absorbing.
- Film and camera applications.
- Floor marking and covering.
- Temporarily fixing and covering cable joints.

Construction

Adhesive	natural rubber
Carrier	polyester/cotton cloth with PE coating matt black

Technical details

Thickness	0,30 mm
Adhesive strength	10 N/25 mm
Tensile strength	157 N/25 mm
Temperature resistance	+60°C
Short term temperature	+80°C
UV resistance	limited
Elongation	11,50%
Mesh	80

Art. No.	width	length	colour	Pack.	EAN code
GB5025	48 mm	25 m	matt black	30	5425014220032
GB4850	48 mm	50 m	matt black	18	5407004560939

Recommendations for use

Temperature: between -5°C and 35°C. The surface should be clean, dry, free of dust and grease. Avoid touching the adhesive side of the tape during the application to avoid affecting its performance. Apply pressure-sensitive tapes under maximum pressure to achieve the optimum pressure level. The indicated performance level is reached after an adhesion time of 24 hours at +23°C.

Storage and shelf life

Clean and dry in a well-ventilated area, preferably at a temperature between +10°C and +30°C. Stored under these conditions, the shelf life will be at least 24 months.

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu

Latest version 03/05/2021