



Adapter

Model: **AK-SC-40**



Product code	AK-SC-40
Product type	Adapter
Responsible Entity	Akyga Europe Sp. z o.o., 52-200 Suchy Dwór, Wrocławska 1c, Polska/Poland, contact@akyga.com
Maximum power	60 W (20 V / 3 A)
Cable length	1 m
The cable plug #1	USB Male connector type C
The cable plug #2	Without termination
Product color	White
Package	UniBag
Package size (L x W x H)	180 x 130 x 6 mm
Net weight	17 g
Gross weight	22 g
EAN code	5906708750375
Warranty	24 months



Description

The **Akyga® AK-SC-40 USB-C repair cable** is a practical solution designed to repair power supplies and chargers for mobile devices. The cable features exposed wires, **ready to be soldered**, making it an ideal choice for those looking for a quick and safe way to replace a damaged cable. Thanks to its durable materials and simple assembly, it is perfect for both the DIY workshop and professional service.

Practical Length and Ease of Use

The **Akyga® AK-SC-40 one-metre long cable** provides optimal charging conditions for mobile devices - it is long enough to freely connect the charger to a phone, tablet or other USB Type C device. What's more, the white colour of the cable preserves the aesthetics and functionality of the repaired equipment.

Up to 60 W Power - Fast and Efficient Charging

The Akyga® AK-SC-40 USB-C service cable is suitable for power supplies **up to 60 W** (20 V / 3 A). This makes it ideal for repairing higher-powered laptop power supplies and chargers for smartphones, tablets and ultrabooks equipped with a USB-C connector.

USB-C Service Cable - Ideal for Repairs

The AK-SC-40 repair cable features a standard USB-C connector on one end and two exposed wires on the other, allowing easy soldering to circuit boards or service connectors. This solution allows you to quickly replace a damaged cable on the charger without having to invest in a new power supply. It will also be perfect for building your own power supply circuits.