

EXTERNAL M.2 SSD NVME & NGFF ENCLOSURE



HIGH SPEED



PLUG & PLAY



COMPATIBILITY



PORTABLE



EN EXTERNAL M.2 SSD NVME & NGFF ENCLOSURE

Interface:	USB 3.1 Gen 2
Maximum Bandwidth:	10 Gbps
Maximum Installed Drive Capacity:	4 TB
Supported drives size:	M.2 2230, M.2 2242, M.2 2260, M.2 2280
Supported drives type:	M.2 (PCI-E, SATA)
Compatibility:	Windows XP / Vista / 7 / 8 / 10 / 11 / macOS



The SAVIO AK-84 is a modern enclosure that effortlessly transforms an internal M.2 SSD (both NVMe and NGFF) into portable, extremely high-performance external storage. With support for USB 3.1 Gen 2, you can achieve data transfer speeds of up to 10 Gbps, allowing for the lightning-fast transfer of even the largest files. This universal solution is compatible with drives up to 4 TB in capacity and all popular sizes (2230, 2242, 2260, 2280). The enclosure operates using Plug & Play with both Windows and macOS systems, eliminating the need to install additional drivers. The durable yet exceptionally light construction (44g) and compact design mean the SAVIO AK-84 takes up minimal space and fits into any bag or backpack. It's also resistant to damage. It offers quick and intuitive disk installation: simply slide the M.2 drive in at an angle, secure it with the latch, and screw the enclosure shut. The set includes a USB-A to USB-C cable and a mounting kit. This is the ideal choice for anyone who values mobility, speed, and security.