


MONITOR DESK MOUNT

17" – 32"



17" – 32"
SCREEN SIZE



UP TO 9 KG
WEIGHT
CAPACITY



NO
PROGRAMMING



ERGONOMIC
SCREEN
SETTING



CABLE
MANAGEMENT



EN ADJUSTABLE MONITOR DESK MOUNT 17" – 32"

Screen size compatibility:	17" – 32"
Max weight capacity:	Up to 9 kg
VESA compatibility:	75 × 75, 100 × 100
Tilt range:	+ 45° ~ - 45°
Swivel range:	+ 90° ~ - 90°
Screen rotation:	+ 180° ~ - 180°
Arm full extension:	403 mm
Material:	Steel, plastic
Surface finish:	Powder coating
Dimensions of product:	116 × 484 × 561 mm
Weight of product:	2.6 kg
Color:	Black
Installation:	Clamp, grommet
Desktop thickness for clamp :	10 – 85 mm
Desktop thickness for cables grommet:	10 – 40 mm
Package content:	Monitor desk mount, mounting elements, user manual



The Savio UM-02 adjustable monitor desk mount is a solid and stylish solution for your workstation or gaming setup. It supports monitors from 17" to 32" weighing up to 9 kg, offering full adjustment of tilt (+45°/-45°), swivel (+90°/-90°), and screen rotation (+180°/-180°). This allows you to perfectly position your monitor for optimal comfort and healthy posture during work or play.

With an arm reach of up to 403 mm, the mount provides great flexibility in positioning. Its sturdy construction, made from steel and plastic and coated with durable powder paint, ensures reliability and a modern look. Installation is quick and non-invasive – you can use either a desk clamp (for desktops 10–85 mm thick) or a grommet mount (for desktops 10–40 mm thick).

Compatibility with VESA 75x75 and 100x100 makes it suitable for a wide range of monitors. The set includes all necessary mounting hardware and an instruction manual. The UM-02 mount helps you keep your desk tidy and organized. It's the perfect choice for those who value ergonomics, aesthetics, and functionality in one.