



USB Cable

Model: **AK-USB-66**



Product code	AK-USB-66
Product type	USB Cable
Responsible Entity	Akyga Europe Sp. z o.o., 52-200 Suchy Dwór, Wrocławska 1c, Polska/Poland, contact@akyga.com
Maximum power	60 W (20 V / 3 A)
Cable length	1 m
The cable plug #1	USB Male connector type C
The cable plug #2	USB Male connector type C
Data transmission	Yes
Version	USB 2.0
Plated plugs	Yes - nickel plated
Cable material	Copper
Material	Silicone
Product color	Pink
Package	UniBag
Package size (L x W x H)	120 x 40 x 20 mm
Net weight	29 g
Gross weight	32 g
CE compatibility	Yes
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5906708750740
Warranty	24 months



Description

Akyga® AK-USB-66 is a high-quality **silicone USB-C to USB-C cable** designed for users who value reliability and modern design. With a maximum charging power of **60 W**, it is perfect for powering laptops, smartphones, tablets and other devices that support Power Delivery technology.

Silicone USB-C cable for fast charging and data transfer

This **1-metre silicone USB-C cable** supports fast charging and stable data transfer, allowing you to quickly recharge your battery or transfer files between devices. The USB-C standard provides a modern and universal connection that fits most modern mobile devices.

Silicone coating — flexibility and durability

The soft, matte silicone coating makes the cable extremely flexible and resistant to mechanical damage such as kinks or abrasions. This makes it ideal for everyday use, while its tangle-resistant design ensures easy storage in a bag.

Modern design

The pink colour adds elegance and freshness to the cable, perfectly complementing modern devices. It is an excellent choice for those who want to combine functionality with a fashionable look.