



Product: [9L28014](#)

Flat Gray Ribbon Cable .050" Pitch, 9L280XX Series, #28-14c, PVC Ins

Product Description

Flat Gray Ribbon Cable .050" Pitch, 9L280XX Series, 14 Conductor, 28 AWG (7x36) Tinned Copper, PVC Insulation

Technical Specifications

Product Overview

Suitable Applications:	Internal interconnection, internal wiring of electronic equipment, reliable mass-termination to standard IDC connectors
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material
28	7x36	TC - Tinned Copper

Conductor Count:	14
------------------	----

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.010 in

Color Chart

Color
Gray

Color Chart1 Table Notes:	First Conductor has Red Stripe
---------------------------	--------------------------------

Construction and Dimensions

Conductor Spacing:	.050 +/- .002 in
Conductor Spacing Center-Center Outside:	.650 +/- .008 in
OuterJacket1, Nominal Width:	.700 +/- .008 in
OuterJacket1, Nom Thick Flat Section:	0.035 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
68.2 Ohm/1000ft

Capacitance

Element	Nom. Capacitance Conductor to Conductor
@ 1 kHz (GSG)	18 pF/ft
@ 1 MHz (GS)	10 pF/ft
@ 1 MHz (GSG)	15 pF/ft

Min Insulation Resistance:	10,000 MOhm
----------------------------	-------------

Inductance

Element	Nominal Inductance
@ 1 MHz (GS)	0.29 µH/ft

@ 1 MHz (GSG)	0.2 µH/ft
---------------	-----------

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Impedance Description
150 Ohm	(GS)
105 Ohm	(GSG)

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
10 MHz	2.8 dB/100ft
20 MHz	4.8 dB/100ft
30 MHz	6.5 dB/100ft
40 MHz	8.3 dB/100ft
50 MHz	9.8 dB/100ft
60 MHz	12 dB/100ft
70 MHz	13 dB/100ft
80 MHz	14 dB/100ft
90 MHz	15.8 dB/100ft
100 MHz	17 dB/100ft

High Frequency Table (Nominal/Typical) Notes:	GSG=Ground-Signal-Ground Mode
---	-------------------------------

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.4 ns/ft	72%

Unbalanced Crosstalk

Element	Typical Unbalanced NEXT %	Typical Unbalanced FEXT %	Typical Cross Talk Pulse Rise Time (ns)
10 ft. sample length	4.8	7	3 ns
10 ft. sample length	3.5	4.7	5 ns
10 ft. sample length	3	3	7 ns

Current

Max. Recommended Current [A]
1 Amp per Conductor at 20°C

Voltage

Dielectric Withstand Voltage	UL Voltage Rating
2000 V	300 V

Temperature Range

Operating Temperature Range:	-40°C to +105°C
------------------------------	-----------------

Mechanical Characteristics

Bulk Cable Weight:	16 lbs/1000ft
Minimum Bend Radius During Installation:	2.55 in
Minimum Minor Axis Bend Radius:	2.52 in

Standards

UL AWM Style Compliance:	AWM 2651
CSA AWM Compliance:	I A

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65 (CJ for Wire and Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Length	UPC
9L28014 008H100	Gray	100 ft	612825221616
9L28014 008H300	Gray	300 ft	612825221623

History

Update and Revision:	Revision Number: 0.397 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.