



1) Tapered thread end max. 4P 2) Trilobular

BN 4908

Pozi pan head thread forming screws

type C, form Z, metric thread

Stainless steel A2

- ~UNI 8112
- Waxed



A technical brochure is available on request

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1183494	M2,5	5	2,12	1	2,6	1,27	1,52	5
1183508								6
1183516								8
1183524								10
1183532	M3	6	2,52	1	3	1,68	1,93	5
1183540								6
1183559								8
1183575								10
1183583								12
1183591								16
1183605								20
1183613	M4	8	3,25	2	4,3	1,9	2,36	6
1183621								8
1183648								10
1183656								12
1183664								16
1183672								20
1578448								25
1578456								30
1183680	M5	10	3,95	2	5	2,64	3,1	8
1183699								10
1183702								12
1183729								16
1183737								20

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1578464	M5	10	3,95	2	5	2,64	3,1	25
1578472								30
1183745	M6	12	4,75	3	6,7	3,02	3,48	10
1183753								12
1183761								16
1183788								20
1183818								25
1578480								30