

MNX ABS 100/50 LT



Sample photo

Order symbol: ABS 100/50 LT
Product nbr: 6082902
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074052414
El. number:
 Finland: 3420582
 Denmark: 8212023783
 Sweden: 6082902
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height
mm:		130	80	50
inch:		5.1	3.1	2.0
Materials:				
Material:		ABS		
Base colour:		RAL 7035		
Cover colour:		Smoked grey		
Cover screws material:		Polyamide		
Cover screws colour:		Black		
Gasket material:		TPE		
Temperatures:				
Short term:		-40 ... 80 °C		
Continuous:		-40 ... 60 °C		
Short term:		-40 ... 175 °F		
Continuous:		-40 ... 140 °F		
Accessories:				
MIV 100		Mounting plate (Galvanized steel)		
MIN 5		DIN-15 Mounting rail		
MIN 10		DIN-15 Mounting rail		
MIV 5		DIN-35 Mounting rail		
MIV 10		DIN-35 Mounting rail		
FP A 100/130		Front plate (Aluminium)		
HFP 130		Front plate hinge series		
FP 22046		Wall fastening lug (4 pcs)		

