

MNX ABS 100/75 HT



Sample photo

Order symbol: ABS 100/75 HT
Product nbr: 6081902
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074024466
El. number:
Finland: 3422257
Denmark: 8212023796
Italy: 7362027
Sweden: 2535813
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm: 130	80	75		Ingress Protection (EN 60529): IP 66/67
inch: 5.1	3.1	3.0		Impact Resistance (EN 62262): IK 07
Materials:				Electrical insulation: Totally insulated
Material: ABS				Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour: RAL 7035				Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour: Smoked grey				Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material: Polyamide				NEMA Class: NEMA 1, 4, 4X, 6
Cover screws colour: Black				Certificates:
Gasket material: TPE				Fimko
Temperatures:				Europe EN 62208: 2003
Short term: -40 ... 80 °C				Gost R
Continuous: -40 ... 60 °C				
Short term: -40 ... 175 °F				
Continuous: -40 ... 140 °F				
Accessories:				
MIV 100	Mounting plate (Galvanized steel)			
MIN 5	DIN-15 Mounting rail			
MIN 10	DIN-15 Mounting rail			
MIV 5	DIN-35 Mounting rail			
MIV 10	DIN-35 Mounting rail			
FP A 100/130	Front plate (Aluminium)			
HFP 130	Front plate hinge series			
FP 22046	Wall fastening lug (4 pcs)			

