



Sample photo

Order symbol: ABS 150/50 LG
Product nbr: 6082314
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074022905
EI. number:
Finland: 3420545
Denmark: 8212023233
Italy: 7361075
Sweden: 2535742
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm: 180	130	50		Ingress Protection (EN 60529): IP 66/67
inch: 7.1	5.1	2.0		Impact Resistance (EN 62262): IK 07
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:	RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:	Polyamide			NEMA Class: NEMA 1, 4, 4X, 6
Cover screws colour:	Grey			
Gasket material:	TPE			
Temperatures:				Certificates:
Short term:	-40 ... 80 °C			Fimko
Continuous:	-40 ... 60 °C			Europe EN 62208: 2003
Short term:	-40 ... 175 °F			Gost R
Continuous:	-40 ... 140 °F			
Accessories:				
MIV 150	Mounting plate (Galvanized steel)			
MIN 10	DIN-15 Mounting rail			
MIN 15	DIN-15 Mounting rail			
MIV 10	DIN-35 Mounting rail			
MIV 15	DIN-35 Mounting rail			
FP A 150/180	Front plate (Aluminium)			
HFP 180	Front plate hinge series			
FP 22046	Wall fastening lug (4 pcs)			

