



DIN 976-1 B

4.6 / 5.6 / 5.8

Nach Wahl des Herstellers

**BN 425****Gewindebolzen**

mit Kuppe

Stahl 4.6 / 5.6 / 5.8

verzinkt-blau

- ~UNI 6610



DIN 976-1 A (ohne Kuppe) auf Anfrage lieferbar

Article#	d ₁	L
1174886	M3	12
1174894		16
1369016		20
1369024		25
1369032		30
1369040		35
1369059		40
1369067		45
1369075		50
1369083		60
1369091		70
1174959	M4	10
1174967		12
1174975		16
1174983		20
1369105		25
1369113		30
1369121		35
1369148		40
1369156		45
1369164		50
1369172		60
1369180		70
1065556		80
1065572		90
1065637		100

Article#	d1	L
1175017	M5	16
1175025		20
1175033		25
1429191		30
1429167		40
1429175		50
1139339		60
1429183		70
1069942		80
1069985		90
1070126		100
1070134		120
1175068	M6	16
1175076		20
1175084		25
1175092		30
1369199		35
1369202		40
1369210		45
1369229		50
1369237		60
1369245		70
1369253		80
1369261		90
1369288		100
1070150		120
1422472		130
1422480		140
1422499		150
1419390	M8	16
1419404		20
1419412		25
1419420		30
1419439		35
1419447		40
1369296		45
1369318		50
1369326		60
1369334		70
1369342		80
1369350		90

Article#	d ₁	L
1369369	M8	100
1422502		120
1422510		130
1422529		140
1422901		150
1419455	M10	20
1419463		25
1419471		30
1419498		35
1419501		40
1419528		45
1419536		50
1369377		60
1369385		70
1369393		80
1369407		90
1369415		100
1422928		120
1422936		130
1422944		140
1422952		150
1369423	M12	30
1369431		40
1369458		50
1369466		60
1369474		70
1369482		80
1369490		90
1369504		100
1369512		110
1369520		120
1369539		130
1369547		140
1369555		150
3129492		200