



BN 684

Zylinderstifte

INOX A1 / A2

- ~VSM 12771 B
- ~UNI 1707
- ~CSN 022150
- INOX A1/A2: nach Wahl des Herstellers
- Toleranz: h8

Article#	d ₁	c~	L
1117203	1	0,2	4
1117211			5
1255525			6
1255533			8
1255541			10
1255568			12
1117238	1,5	0,3	4
1117246			5
1255576			6
1255584			8
1255592			10
1255606			12
1117254			14
1117262			16
1117270			20
1117289	2	0,35	4
1117297			5
1255614			6
1255622			8
1255630			10
1255649			12
1255657			14
1255665			16
1255673			20
1255681			25
1117300	2,5	0,4	4
1117319			5

Article#	d ₁	c~	L
1255703	2,5	0,4	6
1255711			8
1255738			10
1255746			12
1255754			14
1255762			16
1255770			20
1255789			25
1255797	3	0,5	6
1255800			8
1255819			10
1255827			12
1255835			14
1255843			16
1255851			20
1255878			25
1255886			30
1117327			40
1255894	4	0,63	6
1255908			8
1255916			10
1255924			12
1255932			14
1255940			16
1255959			20
1255967			25
1255975			30
1255983			40
1117335			50
1213288	5	0,8	6
1255991			8
1256009			10
1256017			12
1256025			14
1256033			16
1256041			20
1256068			25
1256076			30
1256084			40
1256092			50
1256106			60

Article#	d ₁	c~	L
1256114	6	1,2	10
1256122			12
1256130			14
1256149			16
1256157			20
1256165			25
1256173			30
1256181			40
1256203			50
1256211			60
1213296	8	1,6	16
1256238			20
1397389			25
1256246			30
1256254			40
1256262			50
1256270			60
1256289	10	2	20
1256297			25
1256300			30
1256319			40
1256327			50
1256335			60