



BN 685

Konische Stifte

INOX A1

- ~VSM 12770 B
- ~UNI 7283
- ~CSN 022153
- Toleranz: h10

Article#	d ₁	a~	L
1256416	1,5	0,2	8
1256424			10
1256432			12
1256491	2	0,25	8
1256505			10
1256513			12
1256521			14
1256548			16
1256564			20
1256629	2,5	0,3	16
1256645			20
1256750	3	0,4	16
1256777			20
1256785			25
1256807			30
1256815			35
1256823			40
1256858	4	0,5	16
1256874			20
1256882			25
1256904			30
1256912			35
1256920			40
1256939			45
1256947			50

Article#	d ₁	a~	L
1256971	5	0,63	20
1256998			25
1257013			30
1257021			35
1257048			40
1257064			50
1257099	6	0,8	20
1257102			25
1257129			30
1257137			35
1257145			40
1257153			45
1257161			50
1257188			60
1257196			80
1257218			100
1257226	8	1	30
1257234			35
1257242			40
1257269			50
1257277			60
1257285			80
1257374	10	1,2	60
1257382			80
1257390			100