



Order symbol: CAB PC 203018 G
Product nbr: 8113331
Description: Cabinet, PC, Grey door
Remarks: Latch on the short side

EAN: 6418074020024
El. number:
Finland: 3424103
Electric No. Denmark: 8212020401
Electric No. Italy: 7821010
Electric No. Sweden: 2539963

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Sample photo

Dimensions:				Accessories:	
Length	Width	Height			
mm:	300	200	180	EKIV 17	DIN-35 Mounting rail
inch:	11.8	7.9	7.1	DS35170E1	DIN-35 Mounting rail
Materials:				EKIV 27	DIN-35 Mounting rail
Material:	Polycarbonate			DS35270E1	DIN-35 Mounting rail
Base colour:	RAL 7035 -light grey			FP A 23	Swing-out door/Front plate
Cover colour:	RAL 7035 -light grey			MB 12225 AL	Swing door set
Gasket material:	Polyurethane			FP 23	Front plate
Temperatures:				FP 12-23	Front plate
Temperature °C (short term):	-40 ... 120 °C			DRF 23	DIN rail frame set
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:				Rating:	
EKIV 23	Mounting plate			Ingress Protection (EN 60529): IP65	
				Impact Resistance (EN 62262): IK08	
				Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				Certificates:	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Lloyds Register of Shipping (LR)	
				Gost R	

