



JUNCTION BOX

HP 150-L

HP 150-L

Junction box

164 x 119 x 77 mm

Article number: 32695001

Junction box, Ui=690V, 10 recessed stepped nipples, seal range 5 - 21 mm

Grey, without terminals, with cover retainer



Technical data

Measures

Width:	164 mm
Length:	119 mm
Height:	77 mm
Inner height:	70 mm
Inner width:	155 mm

Material:

Box:	polypropylene, flame-retardent
Cover:	polypropylene, flame-retardent
material:	Polypropylene

Accessory

NS 35-90 - Standard rail

NS 35-106 - Standard rail

NS 35-144 - Standard rail

WK 100 KLS-10² - Terminal block

KVR M25-MGM - Cable gland

SNI M25 - Stepped nipple

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%



JUNCTION BOX

HP 150-L

Other attributes

Equipment:	None
Entries:	11
Tackable:	No
Rated insulation voltage AC:	690 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No