



JUNCTION BOX

HP 190-L

HP 190-L

Junction box

199 x 149 x 77 mm

Article number: 32699001

Junction box, Ui=690V, 10 recessed stepped nipples, seal range 13 - 26.5 mm

Grey, without terminals, with cover retainer



Technical data

Measures

Width:	199 mm
Length:	149 mm
Height:	77 mm
Inner height:	70 mm
Inner width:	190 mm

Material:

Box:	polypropylene, flame-retardent
Cover:	polypropylene, flame-retardent
material:	Polypropylene

Accessory

WK 100 KLS-10² - Terminal block

KS M25-gro - Combi set

NS 35-90 - Standard rail

NS 35-106 - Standard rail

TK MPI-1811 - Mounting plate

NS 35-144 - Standard rail

ADR M25 - Sealing ring

ADR M40 - Sealing ring

AST M25 - Attachment bushes

AST M25-or - Attachment bushes

AST M40 - Attachment bushes

AST M40-or - Attachment bushes

DMS M25 - Double-membrane seals

DMS M25/sw - Double-membrane seals

DST M40 or - Double end connector

GMU PA M25 - Lock nut



JUNCTION BOX

HP 190-L

Other attributes

Equipment:	None
Entries:	14
Tackable:	No
Rated insulation voltage AC:	690 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%