



JUNCTION BOX

i 16-L



i 16-L

Junction box

130 x 85 x 37 mm

Article number: 33391601

Junction box acc. to DIN EN 60670 (VDE 0606), 16 entries, 3 floor entries, complete with punching tool and blanking plug, with external fixing positions

Grey, without terminals, for VDE approved single terminals



Technical data

Measures

Width:	130 mm
Length:	85 mm
Height:	37 mm

Material:

Box:	polyethylene
Cover:	Polypropylene
material:	Polypropylene

Certificates



Accessory

VST RR - Sealing plugs

HandyGrip VG 20 - Terminal strip

HandyGrip VG 21 - Terminal strip

HandyGrip VG 21 w - Terminal strip

HandyQuick SQ 32 - Screwless terminal

HandyQuick SQ 52 - Screwless terminal



JUNCTION BOX

i 16-L

Other attributes

Color:	Grey
Rated cross section:	2,5 mm²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%