

Technical Datasheet



tasker® C275 L.S.Z.H. – 2x1,50 mm²

Halogen Free

Flexible Speaker Cable

FirestoP®



CATEGORY Flexible Speaker Cable (See Audio Catalogue)
APPLICATIONS Professional Loudspeakers and premade cables

- A:** Black **L.S.Z.H.** sheath. Flame Retardant and Halogen Free.
Outdoor Limited. Outer cable Diam. Ø 8,00 (±0,10) mm.
- B:** Core Insulation with PVC Sheath, colored one Red and one Black.
Diam. Ø: 3,00 (±0,10) mm.
- C:** O.F.C. red copper formation 48x0,20 mm.
Nom. Cross section 2x1,50 mm².

MARKING **tasker® C275 L.S.Z.H. 2x1.50 mm² – O.F.C. Speaker Cable – Halogen Free – FirestoP® – Made In Italy**

CUSTOM PRODUCTION This product may be custom produced also in **PVC, PE, PUR,** or Metallic Armored.

Cable Properties

Conductor Resistance	12,50 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-30/+70°C

USE	X	Indoor	Interno Edificio
Impiego	X	Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. A / 16.05.16