

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
20090 Cusago (MI) Italy
T. +39 02 9039.4556-4158
F. +39 02 9039.4551
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
20090 Cusago (MI) Italy
T. +39 02 9039.0037-0059
F. +39 02 9039.0049
www.tasker.it

Technical Datasheet

tasker® C276 L.S.Z.H. – 2x2,50 mm²

Halogen Free

Flexible Loudspeaker Cable

FirestoP®



CATEGORY Flexible Speaker Cable (See Audio Catalogue)
APPLICATIONS Professional Loudspeakers and premade cables

- A:** Black Soft **L.S.Z.H.** sheath. Flame Retardant and Halogen Free.
Outer Diam. Ø 9,00 (±0,20) mm.
- B:** Cores Insulation with **PVC** sheaths colored one Red and one Black.
Diam. Ø 3,50 mm (±0,20) mm.
- C:** O.F.C. red copper formation 80x0,20 mm.
Nom. Cross section 2x2,50 mm²

MARKING **tasker® C276 L.S.Z.H. 2x2,50 mm² – O.F.C. Speaker Cable – Halogen Free - FirestoP® - Made In Italy**

CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE**, **PUR**, with or without Metallic Armor.

Cable Properties

Conductor Resistance	6,41 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-30/+70°C

USE	X	Indoor	Interno Edificio
Impiego	X	Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. A / 16.05.16