








THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE313A0305	2013-09-07	Raison	Modify Jack,Note.Change H Cut
C	LEN1440092	2014-04-04	Tom_gu	Change H Cut To D Cut



Recommended
Panel Cut-out
Rear View



- Note:
- * $\varnothing$ Important Dimension
 - * Waterproof Rate : IP67 Mated
 - * Housing : Nylon+GF,UL 94V-0,BLACK
 - * Screw Nut : Nylon+GF,BLACK
 - * Gasket : Silicone,UL 94V-0,Gray.
 - * PCB: FR-4
 - * Jack : PBT Polyester UL 94V-0
 - * Use without Waterproof cap or Dust cap
For Panel Thickness Max: 4.2mm
 - * Use with Waterproof cap or Dust cap
For Panel Thickness Max: 3.0mm
 - * Screw torsion value range: 8~12kgf-cm

UNIT:mm		TITLE RJ45,C SIZE,MATED WP		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO RCP-5SPFFH-SCM700I	DRAWN BY Tom_gu	DATE 2014-04-04
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 1:1	SIZE A4	SHEET 1 OF 1		DWG NO RCP-5SPFFH-SCM700I	CHECKED BY Tony	DATE 2014-04-04
REV. C		WC-REV. C.2	$\varnothing$ Inspection item			CUSTOMER ALTW	APPROVED BY Victor	DATE 2014-04-04