

Stamped contacts Crimp male contacts diameter 1,6 mm for wire gauge AWG 26 - 20 gold plated

Part No. VN 01 016 0011 (2)

Series Contacts
Subseries Contact Stamped contacts



COMMON CHARACTERISTICS		
Contact diameter		1,6 mm
Insulation diameter		1,0-2,0 mm
Wire gauge from		0,14
Wire gauge to		0,5
Wire gauge (AWG) from		26
Wire gauge (AWG) to		20
Packaging / supplied as		Single contact
No. of pieces		2.000
Sex of Contact		Pin
Type of contact		Stamped/rolled crimp contact
ELECTRICAL CHARACTERISTICS		
Contact resistance	DIN EN 60512-2-1, Test 2a / IEC 60512-2-1, Test 2a	< 5 mΩ

