

所要数 (Req) *	DRWG. <i>2. A WING. 7/27 '77</i>
	DSN'D <i>11. ENO AUTO '76</i>
	CHK'D <i>KE Shie-i</i>
	APP'D
 MOLEX-JAPAN CO., LTD. 日本モレックス株式会社	
No. SD - 5025-03P *	REV. D

CONN. 3POS. PLUG HSG.

5

4

3

2

1

F



E

D

C




B

A



パネル板厚 2mm MAX

パネルスロット寸法



一般公差

10 未満	±0.2
10以上30未満	±0.25
30 以上	±0.3
角度	±3°

15-31-1033	5025-03P1	無
15-31-1031	5025-03P	有
EDP NO.	ENG. NO.	MTG. EAR

					公差 (Tolerances)	所要数 (Req)	DRWG. <i>J. Awano</i> 9/27 '77
					.000 → ±0.005 .00 → ±0.05		DSN'D <i>M. ENO</i> 10/19/77
					.0 → ±0.1 . → ±0.3		CHK'D <i>W. Shiraishi</i>
					材料 (MAT'L)	☆	APP'D <i>W. Shiraishi</i>
E	REVISED ECN.NO. 1499	11/30/77	K.H.		NYLON66, 94V-Z		molex MOLEX-JAPAN CO., LTD. 日本モレックス株式会社
D	ADDED -03P1 ECN.NO. 917	9/5/77			熱処理 (H.T.)		
C	REMOVED "X" ECN.NO. 748	3/18/78			HRc ——— # ———		
B	リブ, パネルスロット, ガーネットNO.	12/16/77			仕上げ (Finish)	No.	
A	REVISED	10/28/77			———— # ———	SD - 5025-03P*	
O	PROPOSED	9/27/77			Scale 2/1	名称 (Name)	REV. E
記号 (LTR)	変更内容 (Rev.)	Date	Name	MINI. FIT CONN. 3POS. PLUG HSG.			