



SAMI6B-XXG03

01:MPQ/REEL
02:LOOSE PIECE 500PCS
03:LOOSE PIECE 100PCS





SECTION A-A



SECTION B-B

Note:

- * Material
Contact Body: Copper Alloy
Outer Spring: Stainless steel
- * Contact Finish: 3u"Min Gold Plating
- * Current Rating: 10A Max
- * Termination Type: Crimping
- * Wire Range: 18AWG~16AWG
- * Salt Spray Test 48H
- * This drawing is supplied for information only design features specifications and performance data



UNIT:mm
TOLERANCE
±0.5

TITLE
10A MALE CLAW PIN TERMINAL
SCALE 3:1
SIZE A4
SHEET 1 OF 1
REV. A
WC-REV. A.3
QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
SAMI6B-XXG03	Jinhai	2015-08-11
ALTW	Rensong	2015-08-11
	Jerry	2015-08-11

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.