





Rating	20A 12VDC	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operating Temperature	-25°C~85°C		
Switch Function	3P SPDT ON-ON (LED dependent)		
		Thickness:2.0~3.0	Thickness:0.7~3.0







Lens

Material:
Frame: Nylon#66, Black
Actuator: Nylon#66, Black
Lens: Clear, PC
Printed: None

Circuit Diagram





07/25/'14	曹盈芳	1.依公司規定追加SCI LOGO 2.依MCN#GRD2010091取消安規刻字			△
Date	Name	Description			NO
Drawn	Checked	Approved	SCI BOM NO.	1823754	Model Name
曹盈芳			Customer No.		Model No.
07/25/'14			Unit	mm	Shin Chin Industrial Co., Ltd.
					Rev. 1