









Rating	20A 14VDC	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P SPDT ON-OFF-ON		



*MATERIAL:
 Frame: Black, Nylon 66 (94-V2)
 Actuator: Black, Nylon 66 (94-V2)
 Lens: Clear, PC (94-V2)
 Terminals: Silver plated, Copper alloy
 Printed: None

Circuit Diagram



C8\R13\R13-112DL-02(1824358)

								△
								△
Date		Name		Description				NO
Drawn	Checked	Approved	SCI BOM No.	1824358		Model Name	ROCKER SWITCH	
曹盈芳	王伯山		Customer No.			Model No.	R13-112DL-02	REV.
11/27/'08	11/27/08	11/27/08	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.			0