









Rating	20A 14VDC	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P SPDT ON-OFF-ON	Thickness:2.0~3.0	Thickness:0.7~3.0



*MATERIAL:
Frame: Black, Nylon 66 (94-V2)
Actuator: Black, Nylon 66 (94-V2)
Lens: Clear, PC (94-V2)
Terminals: Silver plated, Copper alloy
Printed: None

Circuit Diagram



C8\R13\R13-112DL-02(1824360)

Date	Name	Description						NO	
Drawn	Checked	Approved	SCI BOM No.	1824360	Model Name	ROCKER SWITCH			
曹盈芳	王作山	王作山	Customer No.		Model No.	R13-112DL-02	REV.	0	
11/27/'08	11/27/08	11/27/08	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				