









Rating	20A 14VDC	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P SPDT ON-OFF-ON		



*MATERIAL:

Frame: Black, Nylon 66 (94-V2)
 Actuator: Black, Nylon 66 (94-V2)
 Lens: Clear, PC (94-V2)
 Terminals: Silver plated, Copper alloy
 Printed: None

Circuit Diagram



C8\R13\R13-112DL-02(1824359)

									△
									△
									NO
Date	Name	Description							
Drawn	Checked	Approved	SCI BOM No.	1824359	Model Name	ROCKER SWITCH			
曹盈芳	王山	王山	Customer No.		Model No.	R13-112DL-02			REV.
11/27/08	11/27/08	11/27/08	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				0