

ARCA 203015W



Sample photo

Order symbol: ARCA 203015W
Product nbr: 8120140
Description: Cabinet, PC
Remarks: Cover with window, 1-point locking

EAN: 6418074080110
EI. number:
Finland: 3423216
Electric No. 8212091964
Denmark:
Electric No. Sweden: 2500137

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:	Length	Width	Height
mm:	200	300	150
inch:	7.9	11.8	5.9

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover colour: RAL 7035 -light grey
Gasket material: Polyurethane

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Accessories:

MPS ARCA 3020 Mounting plate (250x150x2 mm)

Accessories:

MPP ARCA 2030 Mounting plate perforated (250x150x2 mm - 26x11 mm)
MPMP ARCA 3020 Mounting plate multiperforated (250x150x2 mm - □3.6 mm)
MPX ARCA 3020 Mounting plate (250x150 mm)
DRS ARCA 203015 DIN rail frame set
IDS ARCA 2030 Inner door set
PMK ARCA 30 Pole mounting kit
RCS ARCA 2030 Rain canopy set
SBK ARCA 20 Support bar kit
SBK ARCA 30 Support bar kit

Rating:

Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:

SGS Fimko
Gost R

