

CAB CAB PC 504020 G3B



Sample photo

Order symbol: CAB PC 504020 G3B
Product nbr: 8113362
Description: Cabinet, PC
Remarks: Locks on the long side

EAN:	6418074020369
El. number:	
Finland:	3424124
Electric No.	8212019263
Denmark:	
Electric No. Italy:	7821055
Electric No. Sweden:	2539981

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height
mm:	500	400	200
inch:	19.7	15.7	7.9

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:

EKIV 54	Mounting plate
---------	----------------

Accessories:

EKIV 37	DIN-35 Mounting rail
DS35370E1	DIN-35 Mounting rail
EKIV 47	DIN-35 Mounting rail
DS35470E1	DIN-35 Mounting rail
FP A 54	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 54	Front plate
FP 18X2-54	Front plate
DRF 54	DIN rail frame set

Rating:

Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:

Germanischer Lloyd (GL)
SGS Fimko
Lloyds Register of Shipping (LR)
Gost R

CAB 500x400x200

