

EK EKHA 130 T



Sample photo

Order symbol: EKHA 130 T
Product nbr: 2538101
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074013712
El. number:
Finland: 3425450
Electric No. Italy: 7502010
Electric No. Sweden: 2538101

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	190	190	130
inch:	7.5	7.5	5.1

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover screws material: Polyamide
Cover colour: Clear transparent
Cover screws colour: Grey
Gasket material: Polyurethane

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Accessories:

EKHA Base, PC

Accessories:

EKHS Base, PC
EKH 30-G Cover
EKH 80-G Cover
EKH 30-T Cover
EKH 80-T Cover
EKHVT Mounting plate
EKHXT Mounting plate isolated
EKV 12 DIN-35 Mounting rail

Rating:

Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Certificates:

Germanischer Lloyd (GL)
SGS Fimko
Lloyds Register of Shipping (LR)
Gost R

EK 190x190x130-180

