




Rating	16A 125VAC, 10A 250VAC	cULus	Mounting Hole
	10A 125VAC, 6A 250VAC	CQC	
	10(4)A 250V~		
	20A 12V DC, 10A 24VDC		
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C~85°C		
Switch Function	3P SPDT ON-ON		



Material:






Frame: Nylon#66, Black

Actuator: Nylon#66, Black

Terminals: Cooper Alloy, Silver plating

Printed: None

Circuit Diagram



Tolerances $\pm 0.3\text{mm}$ Unless Otherwise Specified

03/18/'15	曹盈芳	依營業需求增加10A 24VDC				
07/01/'14	黃洋	增加SCI LOGO,更新圖面				
04/23/'10	曹盈芳	為了整合安規取消CSA,追加ENEC/VED10的溫度刻字由T85提升25T85,追加CQC,10A125VAC,6A250VAC,T85刻字				
		依客戶要求Rating追加20A 12V DC				
Date	Name	Description			No.	
Drawn	Checked	Approved	SCI BOM No.	1821150	Model Name	ROCKER SWITCH
曹盈芳		王偉山	Customer No.		Model No.	R13-112C-02
03/18/'15		3/18/15	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 3