








Rating	20A 14V DC	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C ~ 85°C		
Switch Function	4P SPST ON-OFF (LED independent)		

Material:
Frame: Black, Nylon 66
Actuator: Black, Nylon 66
LED: Red

Circuit Diagram



Tolerances ± 0.3 Unless Otherwise Specified

Date	Name	Description				No.
Drawn	Checked	Approved	SCI BOM No.	1810610	Model Name	ROCKER SWITCH
周傑輝	12/11-13	12/12-13	Customer No.		Model No.	R13-112LP-02
12/6/13	12/11-13	12/12-13	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 0