

SKINDICHT® BL-M

SKINDICHT® BL-M, brass blind plugs for closing pre-threaded holes, assembling with screwdriver



Temperature-resistant



Reliability



Robust



Corrosion-resistant

Benefits

For closing pre-threaded holes
Assembling with screwdriver

Application range

Machine and equipment manufacturing
Electric motor manufacturing

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Note

Drawing on request

SKINDICHT® BL-M**Technical Data**

Classification:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
On request:	Fitted with FKM O-ring
Material:	Body: nickel-plated brass Sea water-resistant
Protection rating:	IP 54 IP 68 (with O-Ring)
Temperature range:	With O-ring: -30°C to +100°C Without O-ring: -60°C to +200°C

Note

Photographs are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® BL-M**

Article number	Article designation / size	Outer Ø (mm)
SKINDICHT® BL-M		
52103100	M 12 x 1,5	14
52103110	M 16 x 1,5	18
52103120	M 20 x 1,5	22
52103130	M 25 x 1,5	28
52103140	M 32 x 1,5	35
52103150	M 40 x 1,5	44
52103160	M 50 x 1,5	54
52103170	M 63 x 1,5	70
SKINDICHT® BL-M with O-ring		
52103105	M 12 x 1,5	14
52103115	M 16 x 1,5	18
52103125	M 20 x 1,5	22
52103135	M 25 x 1,5	28
52103145	M 32 x 1,5	35
52103155	M 40 x 1,5	44
52103165	M 50 x 1,5	54
52103175	M 63 x 1,5	70
52103190	M 75 x 1,5	80

Last Update (10.07.2017)

@2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16