




PG 1	PG 2	ϕ A	SW	C	D	E	ϕ F	Artikel Nr. Part. no
9	7	22	20	27	9	15,5	10	5202 5040
11	9	24	22	27	9	15,5	13	5173 0060
13,5	11	27	24	28	10	15,5	14	5173 0070
16	13,5	29	27	28	10	15,5	17	5173 0080

Lieferant: 169003

Toleranzen / tolerances: DIN 160901-140(B)				Werkstoff / material:		Oberfläche / surface		Gewicht / weight:		Volumen / volume:		Farbe / color: RAL	
				Bearb. edited	Datum / date 05.06.1996	Name / name Auner	Geprüft checked	Datum / date 18.06.2007	Name / name M. Zankl		Maßangaben in dimension units		mm
Projektion / projection :		Maßstab / scale: 2:1 (PG11/9)		Benennung / name: SKINDICHT KUS PG DATEN U. MONTAGEBLATT SKINDICHT KUS PG TECHNICAL DATA SHEET									
01	510000000107	22.9.2015 maju2	30.09.2015 Charcenko	 U.I. Lapp GmbH		Zeichnungs-Nr. / drawing no: DM51730060DE_EN						Blatt sheet: 1/1	Dok. Art doc. type LOM
Ind. vs	Änderungs-Nr. change number	Datum / date		 U.I. Lapp GmbH		DM51730060DE_EN						DIN A 4	
		Bearb./edited	Gepr./check.										
				Ersatz für / substitute for: DM51730060DE_EN vs.00									