

SKINTOP® GMP-HF-M

SKINTOP® GMP-HF-M, halogen-free counter nuts, extremely flame-retardant, self-extinguishing, no dripping, for public buildings



Variety of approval certifications



Temperature-resistant



Assembly time



Halogen-free

Benefits

Halogen-free

Extremely flame-retardant according to UL 94 V0

Self-extinguishing, no dripping

Application range

For locking SKINTOP® cable glands in boreholes without thread.

Airports

Tunnel construction

Underground railways

Public buildings

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

SKINTOP® GMP-HF-M

Note

Designed for use with SKINTOP® ST-HF-M

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

Colour delivered:

Light grey (RAL 7035)

Material:

halogenfree polyamide acc. to UL 94 V0

Temperature range:

Fixed: -40°C to +100°C

Dynamic: -20°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® GMP-HF-M**

Article number	Article designation / size	SW wrench size mm
SKINTOP® GMP-HF-M		
53119200	M 12 x 1,5	17
53119210	M 16 x 1,5	22
53119220	M 20 x 1,5	27
53119230	M 25 x 1,5	34
53119240	M 32 x 1,5	41
53119250	M 40 x 1,5	50
53119260	M 50 x 1,5	60
53119270	M 63 x 1,5	75

Last Update (05.04.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16