







PG	M	ΦA	D	C	Art. Nr. Part no.
11	16	20	6	8,5	52104492
16	20	24	6,5	9,5	52104495
21	20	30	7	10	52104497
21	25	30	7	10	52104498
29	25	39	8	11,5	52104500
29	32	39	8	11,5	52104501
36	40	50	9	12,5	52104503

Toleranzen / tolerances: DIN ISO 2768-mH			Werkstoff / material: Messing vernickelt			Oberfläche / surface		Gewicht / weight:		Volumen / volume:		Farbe / color: RAL	
			Bearb. edited	Datum / date 04.07.2000	Name / name M. Schmid	Geprüft checked	Datum / date 01.02.2007	Name / name D. Müller		Maßangaben in dimension units		mm	
Projektion / projection : 			Maßstab / scale: 2:1			Benennung / name: SKINDICHT MA-PG/M DATEN U. MONTAGEBLATT SKINDICHT MA-PG/M TECHNICAL DATA SHEET							
00	500000006331	04.07.2014 mast1	14.01.2015 D. Müller	 U.I. Lapp GmbH			Zeichnungs-Nr. / drawing no.: DM52104492DE_EN					Blatt sheet: 1/1	Dok. Art doc. type LDM
Ind. vs	Änderungs-Nr. change number	Datum / date		 U.I. Lapp GmbH			DM52104492DE_EN					DIN A 4	
		Bearb./edited	Gepr./check.										
Ersatz für / substitute for: BS00_2583_2													