

SILVYN® SCH

SILVYN® SCH - cable clamps



Optimum strain relief

Benefits

Ensures the tensile strength

Clamps various conduit sizes with one clamp

Application range

In combination with:

SILVYN® SSV-M/SSVZ-M

SILVYN® SSV/SSV-Z

Product features

Variable clamping range

Product Make-up

Galvanized steel ring

Worm gear drive

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000127

ETIM 5.0 Class-Description: Fixing clip

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000127

ETIM 6.0 Class-Description: Saddle

Material:

Steel, galvanized

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® SCH**

Article number	Article designation	Clamping range in mm	Suitable for SILVYN® SI/SP/SP-PU
SILVYN® SCH			
52003130	10 - 16 S	10.0 - 16.0	10 x 14 / 11 x 14
52003140	12 - 20 S	12.0 - 20.0	12 x 16 / 13 x 16 / 14 x 18
52003160	16 - 25 S	16.0 - 25.0	16 x 20 / 18 x 22 / 18 x 23
52003170	20 - 32 S	20.0 - 32.0	22 x 27
52009050	25 - 40 S	25.0 - 40.0	30 x 36 / 23 x 28
52009061	35 - 50 S	35.0 - 50.0	32 x 38 / 38 x 44
52009040	40 - 60 S	40.0 - 60.0	45 x 51 / 50 x 56

Last Update (09.04.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16