




Rating	16A 125VAC 1/3HP 10A 250VAC 1/2HP		Mounting Hole	Circuit Diagram	
	10(4)A 250V~ 10E3				
	10A 125VAC, 6A 250VAC				
	CQC				
Contact Resistance	50m ohm Max.				
Insulation Resistance	DC 500V 100M ohm Min.				
Dielectric Strength	AC 1500V 1 minute				
Operation Temperature	-25°C~85°C				
Switch Function	3P SPDT ON-OFF-ON	Thickness	X	Y	
		0.75...1.25	19.2-0.1	13.2+0.1	
		1.25...2	19.4-0.1	13.2+0.1	
		2...3	19.8-0.1	13.2+0.1	

Material:
 Frame: Nylon#66, Black
 Actuator: Nylon#66, Black
 Terminal: Cooper Alloy, Silver plating
 Printed: White, hot stamping



Tolerances $\pm 0.3\text{mm}$ Unless Otherwise Specified



07/02/14	黃洋	依實物增加SCI LOGO,更新圖面.				△	
11/16/10	曹盈芳	本體刻字更新, 重新出圖				△	
Date	Name	Description				NO	
Drawn	Checked	Approved	SCI BOM NO.	1820407	Model Name	ROCKER SWITCH	
黃洋	周木輝	Smile	Customer No.		Model No.	R13-66D-02	Rev.
07/02/14	7/10-14	7/10-14	Unit	mm	Shin Chin Industrial Co., Ltd.		2