

## Technical Datasheet

**tasker® TSK 1170 – 4x0,22 mm<sup>2</sup>**

**FirestoP® Flat Divisible Double Sheath RGB Cable**



A

B

C

### CATEGORY

Flat Multi Conductor Cable ( See Electronics Catalogue)

### APPLICATIONS

Electronics and LED alimentation

- A:** Soft White **Flame Retardant PVC** – RAL 9010.  
Outer cable dimension: 2,5x10,0 (± 0,10) mm
- B:** 4 single conductors sheathed with soft **Flame Retardant PVC** ,  
colored Red, Green, Blue and Black.  
Outer cable Diam. Ø 1,20 (±0,10) mm.
- C:** Stranded O.F.C. red copper formation 7x0.20 mm.  
Nom. Cross section 4x0,22 mm<sup>2</sup>.

### MARKING

**tasker® TSK1170 4x0,22 mm<sup>2</sup> O.F.C. Double Sheath Rgb-Led Strip**  
**Cable FirestoP ®**

### CUSTOM

This product may be custom produced also in **L.S.Z.H. polymer, PE, PUR**

### PRODUCTION

### Cable Properties

|                              |            |
|------------------------------|------------|
| <b>Conductor Resistance</b>  | 79,15 Ω/Km |
| <b>Max Rated Voltage</b>     | 49 V       |
| <b>Operative Temperature</b> | -20/+70°C  |

|                |          |                       |                   |                     |          |                      |                  |                     |          |                   |
|----------------|----------|-----------------------|-------------------|---------------------|----------|----------------------|------------------|---------------------|----------|-------------------|
| <b>USE</b>     | <b>X</b> | Indoor                | Interno Edificio  | <b>INSTALLATION</b> | <b>X</b> | Fixed                | Fissa            | <b>INFORMATION</b>  | <b>X</b> | RoHS2 Compliant   |
| <b>Impiego</b> |          | Outdoor Limited       | Esterno Limitato  | <b>Posa</b>         | <b>X</b> | Restricted Mobile    | Mobile Limitata  | <b>Informazioni</b> | <b>X</b> | Ver. A / 26.05.17 |
|                |          | Outdoor               | Esterno           |                     |          | Mobile               | Mobile           |                     |          |                   |
|                |          | Outdoor Direct Burial | Esterno Interrato |                     |          | Mobile in Drag Chain | Mobile in Catena |                     |          |                   |